



PRODUCT CERTIFICATE

No.: CQC16001160842

NAME AND ADDRESS OF THE APPLICANT

Analog Devices (Shanghai) Co.,Ltd.
5F, Sandhill Plaza,2290 Zuchongzhi Road Zhangjiang Hi-Tech Park,Pudong New District,Shanghai,China

NAME AND ADDRESS OF THE MANUFACTURER

Analog Devices
804 Woburn Street,WilmingtonMA, USA

NAME AND ADDRESS OF THE FACTORY

Analog Devices Gen. Trias (V018387)
Gateway Business Park,Javalera, Geb. Trias,Cavite, Philippines

NAME, MODEL AND SPECIFICATION

Digital Isolator

See Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB4943.1-2011

CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules
CQC11-471543-2015.

Date of issue: Dec.20,2016

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing
certification body until the expiry date.

President:


Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0093673



产品认证证书

证书编号: CQC16001160842

申请人名称及地址

亚德诺半导体技术(上海)有限公司
上海市浦东新区张江高科技园区祖冲之路2290号展想广场5楼

制造商名称及地址

Analog Devices
804 Woburn Street Wilmington MA 美国

生产企业名称及地址

Analog Devices Gen. Trias (V018387)
Gateway Business Park, Javalera, Geb. Trias, Cavite, 菲律宾

产品名称和系列、规格、型号

数字隔离器

见附件

产品标准和技术要求

GB4943.1-2011

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-471543-2015 认证规则的要求, 特发此证。

发证日期: 2016年12月20日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任: _____



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0093673



产品认证证书

附录:

第 1 页 共 1 页

证书编号: CQC16001160842

纸号: 93673

ADuM140D0BRZ, ADuM140D1BRZ, ADuM140E0BRZ, ADuM140E1BRZ, ADuM141D0BRZ,
ADuM141D1BRZ, ADuM141E0BRZ, ADuM141E1BRZ, ADuM142D0BRZ, ADuM142D1BRZ,
ADuM142E0BRZ, ADuM142E1BRZ, ADuM130D0BRZ, ADuM130D1BRZ, ADuM130E0BRZ,
ADuM130E1BRZ, ADuM131D0BRZ, ADuM131D1BRZ, ADuM131E0BRZ, ADuM131E1BRZ,
ADuM132D0BRZ, ADuM132D1BRZ, ADuM132E0BRZ, ADuM132E1BRZ, ADuM140D0WBRZ,
ADuM140D1WBRZ, ADuM140E0WBRZ, ADuM140E1WBRZ, ADuM141D0WBRZ, ADuM141D1WBRZ,
ADuM141E0WBRZ, ADuM141E1WBRZ, ADuM142D0WBRZ, ADuM142D1WBRZ, ADuM142E0WBRZ,
ADuM142E1WBRZ, ADuM130D0WBRZ, ADuM130D1WBRZ, ADuM130E0WBRZ, ADuM130E1WBRZ,
ADuM131D0WBRZ, ADuM131D1WBRZ, ADuM131E0WBRZ, ADuM131E1WBRZ, ADuM132D0WBRZ,
ADuM132D1WBRZ, ADuM132E0WBRZ, ADuM132E1WBRZ: 外部爬电距离: 4.01mm, 通过热循环
测试, 基本绝缘或附加绝缘: (仅适用于海拔 5000 米及以下)

注: 此附录与证书同时使用时有效。

主任: _____



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>