



产品认证证书

证书编号: CQC18001196412

申请人名称及地址

Analog Devices. Inc
804 Woburn Street WilmingtonMA 美国

制造商名称及地址

Analog Devices. Inc
804 Woburn Street WilmingtonMA 美国

生产企业名称及地址

Analog Devices Gen. Trias (V018387)
Gateway Business Park, Javalera, Geb. Trias, Cavite, 菲律宾

产品名称和系列、规格、型号

数字隔离器

见附件 (仅适用于海拔 5000 米及以下)

产品标准和技术要求

GB4943.1-2011

认证模式

产品型式试验+获证后监督

上述产品符合 CQC11-471543-2015 认证规则的要求, 特发此证。

发证日期: 2018 年 06 月 21 日

本证书的有效性依据发证机构的定期监督获得保持。

主任: _____



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

C 0116467



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC18001196412

NAME AND ADDRESS OF THE APPLICANT

Analog Devices, Inc
804 Woburn StreetWilmingtonMA USA

NAME AND ADDRESS OF THE MANUFACTURER

Analog Devices, Inc
804 Woburn StreetWilmingtonMA, USA

NAME AND ADDRESS OF THE FACTORY

Analog Devices Gen. Trias (V018387)
Gateway Business Park,Javalera, Geb. Trias,Cavite, Philippines

PRODUCT NAME, MODEL AND SPECIFICATION

digital isolators
see annex (Altitude up to 5000m)

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB4943.1-2011

TYPE OF CERTIFICATION SCHEMES

Type Testing of Product + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2015 .

Valid from: Jun.21,2018

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0116467



产品认证证书

附录

第 1 页 共 1 页

证书编号: CQC18001196412

纸号: 116467

ADuM150N1BRZ, ADuM150N1BRZ-RL7, ADuM150N0BRZ, ADuM150N0BRZ-RL7,
ADuM151N1BRZ, ADuM151N1BRZ-RL7, ADuM151N0BRZ, ADuM151N0BRZ-RL7,
ADuM152N1BRZ, ADuM152N1BRZ-RL7, ADuM152N0BRZ, ADuM152N0BRZ-RL7,
ADuM160N1BRZ, ADuM160N1BRZ-RL7, ADuM160N0BRZ, ADuM160N0BRZ-RL7,
ADuM161N1BRZ, ADuM161N1BRZ-RL7, ADuM161N0BRZ, ADuM161N0BRZ-RL7,
ADuM162N1BRZ, ADuM162N1BRZ-RL7, ADuM162N0BRZ, ADuM162N0BRZ-RL7,
ADuM163N1BRZ, ADuM163N1BRZ-RL7, ADuM163N0BRZ, ADuM163N0BRZ-RL7,

外部爬电距离: 4.0mm, 通过热循环测试, 基本绝缘或附加绝缘: 最大工作电压: 400V 有效值, 565V 峰值

注: 此附录与证书同时使用时有效。

主任: _____



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>