

Package Outline Drawing (POD) Dimensional Analysis

Body Size (mm)	Lead Count	Punch Type LFCSP				Sawn Type LFCSP			
		POD Spec	E-Pad Size (mm SQ.)	Lead Length (mm)	Lead Width (mm)	POD Spec	E-Pad Size (mm SQ.)	Lead Length (mm)	Lead Width (mm)
6 x 6	36	CP 36-1	3.7 ± 0.15	0.60 ^{+0.15} _{-0.10}	0.28 ^{+0.07} _{-0.05}	CP 36-4	3.7 ^{+0.15} _{-0.10}	0.60 ^{+0.15} _{-0.10}	0.23 ^{+0.07} _{-0.05}
	40	CP 40-8	3.1 ± 0.15	0.40 ± 0.10	0.23 ^{+0.07} _{-0.05}	CP 40-16	3.1 ± 0.15	0.40 ± 0.10	0.23 ^{+0.07} _{-0.05}
		CP 40-1	4.1 ± 0.15	0.40 ± 0.10	0.23 ^{+0.07} _{-0.05}	CP 40-9	4.1 ± 0.15	0.40 ± 0.10	0.25 ^{+0.05} _{-0.07}
7 x 7	48	CP 48-3	4.1 ± 0.15	0.40 ± 0.10	0.23 ^{+0.07} _{-0.05}	CP 48-5	4.1 ± 0.15	0.40 ± 0.05	0.23 ^{+0.07} _{-0.05}
		CP 48-1	5.1 ± 0.15	0.40 ± 0.10	0.23 ^{+0.07} _{-0.05}	CP 48-4	5.1 ± 0.10	0.40 ± 0.05	0.23 ^{+0.07} _{-0.05}