

# PCN 16\_0167

## Qualification Results

TEST NAME	SPECIFICATION	SAMPLE SIZE	RESULTS
High Temp Operating Life	500 Hrs @ +125 °C T-junction minimum	16 (0)	Pass
Temperature Cycle	JESD22, Method A104-A Condition N -40°C to +85°C. 500 Cycles	16 (0)	Pass