

Current Data Sheet Propagation Delay Limits				
ADuM1280, ADUM1281, ADuM1285, ADuM1286 (C grade only)				
5V Operation (From :)				
Specification	Min	Typ	Max	Unit
Propagation Delay	13	18	24	ns

Revised Data Sheet Propagation Delay Limits				
ADuM1280, ADUM1281, ADuM1285, ADuM1286 (C grade only)				
5V Operation (To :)				
Specification	Min	Typ	Max	Unit
Propagation Delay	20	23	29	ns

3V Operation (From :)				
Specification	Min	Typ	Max	Unit
Propagation Delay	20	25	33	ns

3.3V Operation (To :)				
Specification	Min	Typ	Max	Unit
Propagation Delay	22	27	35	ns

Mixed 5V/3V Operation (From :)				
Specification	Min	Typ	Max	Unit
Propagation Delay	13	20	26	ns

Mixed 5V/3.3V Operation (To :)				
Specification	Min	Typ	Max	Unit
Propagation Delay	20	25	31	ns

Mixed 3V/5V Operation (From :)				
Specification	Min	Typ	Max	Unit
Propagation Delay	16	24	30	ns

Mixed 3.3V/5V Operation (To :)				
Specification	Min	Typ	Max	Unit
Propagation Delay	20	27	33	ns