

Current Data Sheet Limits				
ADuM6210, ADuM6211, ADuM6212				
5V Operation (From:)				
Specification	Min	Typ	Max	Unit
Propagation Delay (C grade only)	13	18	24	ns
VISO Setpoint	x	5.0	x	V

3.3V Operation (From:)				
Specification	Min	Typ	Max	Unit
Propagation Delay (C grade only)	20	25	33	ns
VISO Setpoint	x	3.3	x	V

Mixed 5V/3.3V Operation (From:)				
Specification	Min	Typ	Max	Unit
Propagation Delay (C grade only)	13	20	26	ns
VISO Setpoint	x	3.3	x	V

Revised Data Sheet Limits				
ADuM6210, ADuM6211, ADuM6212				
5V Operation (To:)				
Specification	Min	Typ	Max	Unit
Propagation Delay (C grade only)	20	23	29	ns
VISO Setpoint	4.675	5.0	5.325	V

3.3V Operation (To:)				
Specification	Min	Typ	Max	Unit
Propagation Delay (C grade only)	22	27	35	ns
VISO Setpoint	3.135	3.3	3.51	V

Mixed 5V/3.3V Operation (To:)				
Specification	Min	Typ	Max	Unit
Propagation Delay (C grade only)	20	25	31	ns
VISO Setpoint	3.135	3.3	3.51	V