

**PCN 19_0043 Substitution Data for ADIS16375
Qualification of Additional Assembly Site IMI
ADIS16487 Qualification Test Results**

Test Name	Specification	Conditions	Device	Sample Size	Qty. Failures
Temperature Cycling (TC)	JESD22-A104	-40°C/+85°C 1,000 Cycles	ADIS16487	16	0
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=110°C, Biased, 1,000 Hours	ADIS16487	16	0