

Qualification Results Summary
WIN 0.5µm pHEMT, MSL 3 Rating Change for LFCSP Package Devices

QUALIFICATION RESULTS			
TEST	SPECIFICATION	SAMPLE SIZE	RESULTS
Temperature Cycle (TC)*	<i>JEDEC JESD22-A104</i>	1496	Pass
Solder Heat Resistance (SHR)*	<i>JEDEC/IPC J-STD-020</i>	897	Pass

* These samples were subjected to preconditioning (per j-STD-020 Level 3) prior to the start of the stress test. Level 3 preconditioning consists of the following: 1. Bake – 24 hours at 125°C; 2. Soak – unbiased soak for 192 hours at 30°C, 60%RH; 3. Reflow – three passes through a reflow oven with a peak temperature of 260°C.

Qualification Results Summary
WIN 0.5µm pHEMT, MSL 3 Rating Change for MINI SO EP Package Devices

QUALIFICATION RESULTS			
TEST	SPECIFICATION	SAMPLE SIZE	RESULTS
Temperature Cycle (TC)*	<i>JEDEC JESD22-A104</i>	327	Pass
Solder Heat Resistance (SHR)*	<i>JEDEC/IPC J-STD-020</i>	63	Pass

* These samples were subjected to preconditioning (per j-STD-020 Level 3) prior to the start of the stress test. Level 3 preconditioning consists of the following: 1. Bake – 24 hours at 125°C; 2. Soak – unbiased soak for 192 hours at 30°C, 60%RH; 3. Reflow – three passes through a reflow oven with a peak temperature of 260°C.