



Data Sheet Specification Change on VHH Driver for the High-Speed Mode DC Output Current Limits

Data Sheet Comparison ADATE324

ADATE324 Sp0

Page 16

Refer to change below

From:

DC Output Current Limit					
Source	+60	+100	mA	P	VIH = +4.5 V, short output to -0.5 V VIL = 0 V, short output to 5 V
Sink	-100	-60	mA	P	

To:

DC Output Current Limit					
Source	+55	+100	mA	P	VIH = +4.5V, short output to -0.5V
Sink	-100	-55	mA	P	VIL = +0V, short output to +7V