



Data Sheet Revision for AD5428/AD5440/AD5447

Data Sheet Specification Comparison

Previous Rev

New Rev

SPECIFICATIONS

Table 2. (Continued)

Parameter ¹	Limit at T _{MIN} , T _{MAX}	Unit	Conditions/Comments
t ₃	10	ns min	$\overline{\text{CS}}$ low time
t ₄	10	ns typ	Address setup time
t ₅	10	ns typ	Address hold time
t ₆	6	ns min	Data setup time
t ₇	0	ns min	Data hold time
t ₈	5	ns min	R/ $\overline{\text{W}}$ high to $\overline{\text{CS}}$ low
t ₉	7	ns min	$\overline{\text{CS}}$ min high time

SPECIFICATIONS

Table 2. (Continued)

Parameter ¹	Limit at T _{MIN} , T _{MAX}	Unit	Conditions/Comments
t ₃	10	ns min	$\overline{\text{CS}}$ low time
t ₄	-0.5 -2	ns min ns typ	Address setup time
t ₅	10	ns typ	Address hold time
t ₆	6	ns min	Data setup time
t ₇	0	ns min	Data hold time
t ₈	5	ns min	R/ $\overline{\text{W}}$ high to $\overline{\text{CS}}$ low
t ₉	7	ns min	$\overline{\text{CS}}$ min high time