

DWG NO

DC1067A

SH

1

REV

2

ECO

REV

DATE


APPROVED

LTC CONFIDENTIAL – For Customer Use Only


REVISION HISTORY

NOTES: UNLESS OTHERWISE SPECIFIED,

1. ARTWORK P/N DC1067A REV 2.
2. FAB PER IPC-A-600
3. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
FINISHED THICKNESS TO BE 1.6 +/- .127 MM
WITH 2 OZ. COPPER ON TWO OUTER LAYERS AND
FLAMABILITY RATING: 94 V-2 MINIMUM .
4. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
5. BOARD: SELECTIVE PLATED BOARD. SOLDER
MASK OVER BARE COPPER.
GOLD IMMERSION BOTH SIDES.
SOLDER MASK TYPE: WET PHOTO-IMAGEABLE
THE PCB COLOR: GREEN
SILKSCREEN COMPONENT SIDE WITH WHITE
NON-CONDUCTIVE INK.
PLATE THRU ALL HOLES WITH COPPER
MIN. PLATING THICKNESS: 1 OZ. EXCEPT
WHERE PLATING NOT REQUIRED
6. DRILL: ALL HOLES SHALL BE DRILLED +/- .08 MM
WITH RESPECT TO CTR. OF DRILLED PAD.
ALL HOLES FINISHED SIZE AFTER PLATING.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING:



SIZE	QTY	SYM	PLTD	TOL
0.25	40	+	YES	+/-0.08
0.9	22	X	YES	+/-0.08
1.6	4	□	YES	+/-0.13
1.8	2	⊗	NO	+/-0.13



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MILLIMETERS
TOLERANCES ON ANGLE ±1°
.XX ±.25
.XXX ±.127

CONTRACT NO.

APPROVALS

DRAWN

CHECKED

APPROVED

DESIGNED BY

LINEAR TECHNOLOGY

1630 McCarthy Blvd.
Milpitas, CA 95035 .

Phone: (408)432-1900
Fax: (408)434-0507

TITLE

FAB, LTC245XXXX, EVALUATION
BOARD

DATE

02/23/06

SIZE

A

CAGE CODE

DWG NO.

DC1067A

REV

2

SCALE

1/1

FILENAME: 1067A-2.PCB

SHEET

1

OF

1