

ITEM	QTY	REF	DESCRIPTION	MFR PART NUMBER
1	4	C1,C5,C6,C7	CAP, COG, 100pF, 50V, 5%, 0402	MURATA GRP1555C1H101J
2	1	C2	CAP, X7R, .01uF, 16V, 10%, 0402	MURATA GRP155R71C103K
3	1	C3	CAP, Y5V, 1uF, 10V, [+80%,-20%], 0603	TAIYO YUDEN LMK107F105ZA
4	1	C4	CAP, COG, 1.5pF, 50V, +/-0.25pF, 0402	MURATA GRP1555C1H1R5C
5	1	C8	CAP, COG, 6.8pF, 50V, +/-0.5pF, 0402	MURATA GRP1555C1H6R8D
6	1	R1	RES, CHIP, 10 OHM, 1%, 0402	AAC CR05-10R0FM
7	2	L1,L2	IND, 47nH, 5%, 0402	COILCRAFT 0402CS-47NXJB
8	1	L3	IND, 5.6nH, 10%, 0402	TOKO LL1005-FH5N6K
9	1	T1	XFMR, 2:1, HYBRID, 1900MHz +/-100MHz	MURATA LDB211G9010C-001
10	1	T2	XFMR, 8:1, RF, WIDEBAND, 2-500MHz	MINI-CIRCUITS TC8-1
11	1	U1	IC, LT5512EUF, 4X4mm QFN	LINEAR LTC5512EUF
12	3	J1,J2,J3	CONN, SMA, 50-OHM EDGE-LAUNCH	E.F. JOHNSON 142-0701-851
13	3	TP1,TP2,TP3	TESTPOINT, TURRET, .090	MILL-MAX 2501-2
14	1		PCB, DC478B	DEMO BOARD DC478B