



REVISIONS			
REV	DESCRIPTION	APPR	DATE

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4. 4 OZ. COPPER ON OUTER LAYER, 2 OZ. COPPER ON INNER LAYER, THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS. FLAMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER. .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING. HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
5. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING:



FAB Drawing

SIZE	QTY	SYM	PLTD
15	279	+	PLTD
70	2	×	NPLTD
95	4	□	PLTD
195	2	◇	PLTD
65	2	⊠	PLTD

FAB DRAWING

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ±1
2 PLACE ±.01 3 PLACE ±.005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

APPROVALS		INIT		DATE	
DRAWN	CHECK	JUNE WU	6/5/02		
ENGR	KURK M.	6/5/02			

--	--	--	--	--	--