

6/17/2005

Item	Qty	Reference	Part Description	Manufacture / Part #
1	1	CFF	Cap., NPO 22pF 25V 10%	AVX 04023A220KAT2A
2	3	CIN1,COUT2,CIN2	Cap., X5R 100uF 6.3V 20%	TDK C4532X5R0J107M
3	0	CIN3 (Optional)	Cap., X5R 100uF 6.3V 20%	TDK C4532X5R0J107M
		OR		SANYO POSCAP 6TPE150M
4	0	COUT3,CIN4 (Optional)	Cap., X5R 100uF 6.3V 20%	TDK C4532X5R0J107M
5	1	CITH	Cap., X7R 470pF 25V 20%	AVX 04023C471MAT2A
6	1	COUT1	Cap., X5R 100uF 6.3V 20%	TDK C4532X5R0J107M
		OR		SANYO POSCAP 6TPE150M
7	1	CSS	Cap., X7R 1000pF 50V 10%	AVX 06035C102KAT1A
8	1	C1	Cap., NPO 100pF 25V 10%	AVX 04023A101KAT2A
9	2	JP2,JP1	Headers, 3 Pins 2mm Ctrs.	CommConn Con. Inc. 2802S-03G2
10	4	JP3,JP4,JP5,JP6	Jumper, 2pins 2mm Ctrs.	CommConn Con. Inc. 2802S-02G2
11	3	XJP1,XJP2,XJP4	Shunt, 2 Pins 2mm Ctrs.	CommConn Con. Inc. CCIJ2MM-138G
12	1	L1	Inductor, 0.47uH	VISHAY IHLP-2525CZ-47
13	1	RFB1	Res., Chip 255K 1/16W 1%	AAC CR05-2553FM
14	1	RFB2	Res., Chip 432K 1/16W 1%	AAC CR05-4323FM
15	1	RFB3	Res., Chip 634K 1/16W 1%	AAC CR05-6343FM
16	0	RFB4 (Optional)	Jumper, Chip 0 1/16W 5%	AAC CJ05-000M
17	1	RITH	Res., Chip 12.1K 1/16W 1%	AAC CR05-1212FM
18	1	RPG	Res., Chip 100K 0.06W 5%	AAC CR05-104JM
19	1	RSS	Res., Chip 2.2M 1/16W 5%	AAC CR05-225JM
20	1	RT	Res., Chip 294K 0.06W 1%	AAC CR05-2943FM
21	1	R1	Res., Chip 78.7K 1/16W 1%	AAC CR05-7872FM
22	1	R2	Res., Chip 124K 1/16W 1%	AAC CR05-1243FM
23	5	TP1,TP2,TP3,TP4,TP5	Turret, Testpoint	Mill Max 2501-2
24	1	U1	I.C., Step-Down Reg.	Linear Tech. Corp. LTC3414EFE
25	4		SCREW, #4-40, 1/4"	ANY
26	4		STANDOFF, #4-40 1/4"	MICRO PLASTICS 14HTSP101
27	1		PRINTED CIRCUIT BOARD	DEMO CIRCUIT 556A
28	1		STENCIL	STENCIL DC556A