


LTC CONFIDENTIAL – For Customer Use Only

DWG NO DC560A		SH 1	REV 3
REVISION HISTORY			
ECO	REV	DATE	APPROVED



COMPONENT SIDE SHOWN

- NOTES: UNLESS OTHERWISE SPECIFIED.
- 1. ARTWORK P/N DC560A REV 3.
 - 2. FAB PER IPC-A-600
 - 3. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .062 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH ON TWO LAYERS. FLAMABILITY RATING: 94 V-2 MINIMUM .
 - 4. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
 - 5. BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER. COLOR: GREEN LPI. WHITE TIN IMMERSION (OMIKRON) BOTH SIDES. SILKSCREEN COMPONENT SIDE WITH WHITE NON-CONDUCTIVE INK. PLATE THRU ALL HOLES WITH COPPER MIN. PLATING THICKNESS: 1 OZ. EXCEPT WHERE PLATING NOT REQUIRED
 - 6. DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.
 - 7. DROP: ALL UNUSED PADS ON INNER LAYERS.
 - 8. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.

HOLE LEGEND

TOLERANCE	SIZE	QTY	SYM	PLTD
+/-0.003	10	19	+	PLTD
+/-0.003	35	6	X	PLTD
+/-0.003	70	2	□	NPLTD
+/-0.005	95	5	◇	PLTD

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON ANGLE ±1 ° 2 PLACE ±.01 3 PLACE ±.005 INTERPRET DIM AND TOL PER ASME Y14.5M - 1994		CONTRACT NO	
THIRD ANGLE PROJECTION 	APPROVALS	DATE	
	DRAWN MEI	07/31/02	
	CHECKED		
	APPROVED		
ENGINEER			
DO NOT SCALE DRAWING			
TITLE FAB, LTC3403, WCDMA CELLULAR PHONE BUCK REGULATOR		SIZE A	REV 3
CAGE CODE		DWG NO DC560A	
SCALE 1/1		FILENAME: 560A-3.PCB	SHEET 1 OF 1



163D McCarthy Blvd.
Milpitas, CA 95035
Phone: (408)432-1900
Fax: (408)434-0507