


LTC CONFIDENTIAL – For Customer Use Only

REVISION HISTORY			
ECO	REV	DESCRIPTION	DATE
			APPROVED



COMPONENT SIDE SHOWN

- NOTES: UNLESS OTHERWISE SPECIFIED,
- ARTWORK P/N DC645A REV 1.
  - FAB PER IPC-A-600
  - MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .082 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH ON TWO LAYERS. FLAMABILITY RATING: 94 V-2 MINIMUM .
  - SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
  - BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER, COLOR, GREEN LPI. WHITE TIN IMMERSION (OMIKRON) BOTH SIDES. SILKSCREEN COMPONENT SIDE WITH WHITE NON-CONDUCTIVE INK.
  - PLATE THRU ALL HOLES WITH COPPER
  - MIN. PLATING THICKNESS: 1 OZ. EXCEPT WHERE PLATING NOT REQUIRED
  - DRILL: ALL HOLES SHALL BE DRILLED +/--.003 INCH WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.
  - DROP ALL UNUSED PADS ON INNER LAYERS.
  - DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.

HOLE LEGEND

TOLERANCE	SIZE	QTY	SYM	PLTD
+/-0.003	10	11	+	PLTD
+/-0.003	35	3	X	PLTD
+/-0.003	70	2	□	NPLTD
+/-0.005	95	5	◇	PLTD

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON ANGLE ±1 ° 2 PLACE ±.01 3 PLACE ±.005 INTERPRET DIM AND TOL PER ASME Y14.5M - 1994	CONTRACT NO		1630 McCarthy Blvd. Milpitas, CA 95035 Phone: (408)432-1900 Fax: (408)434-0507	
	APPROVALS	DATE	TITLE	
	DRAWN MEI	02/10/03	FAB, LTC3408EDD, WCDMA CELLULAR PHONE BUCK REGULATOR	
	CHECKED		SIZE A	CAGE CODE
	APPROVED		DWG NO	DC645A
THIRD ANGLE PROJECTION	ENGINEER		SCALE 1/1	FILENAME: 645A-1PCB
DO NOT SCALE DRAWING			SHEET 1 OF 1	REV 1