

Item	Qty	Ref -Des	Desc	Manufacturer's Part Number
1	1	C1	CAP, 1210 2.2uF 20% 50V X5R	TDK C3225X5R1H225M
2	1	C2	CAP, 1210 47uF 20% 6.3V X5R	TDK C3225X5R0J476M
3	1	C3	CAP, 0603 150pF 10% 25V NPO	AVX 06033A151KAT
4	1	C4	CAP, 0603 18pF 5% 50V NPO	AVX 06035A180JAT
5	1	C5	CAP, 0603 100pF 10% 25V NPO	AVX 06033A101KAT2A
6	1	C6	CAP, 22uF 50V ELEC	SANYO 50CV22BS
7	2	C10,C7	CAP, 0603 1uF 10% 6.3V X5R	AVX 06036D105KAT
8	1	C8	CAP, 0603 0.22uF 10% 16V XR7	TDK C1608X7R1C224K
9	1	C9	CAP, 0603 0.1uF 10% 50V X&R	TDK C1608X7R1H104K
10	1	D1	DIODE, SCHOTTKY BARRIER RECTIFIER	DIODES INC. DFLS140L
11	1	D2	DIODE, SCHOTTKY	CENTRAL SEMI CMDSH-4E
12	0	D3	DO NOT STUFF	CENTRAL SEMI CMDSH-4E OPTION
13	5	E1,E2,E3,E4,E5	TURRET	MILL-MAX 2501-2
14	2	JP1,JP2	HEADER, 3PIN 2mm	COMM CON 2802S-03G1
15	1	L1	IND, 10uH	TOKO A916CY-100M
16	1	R1	RES, 0603 10K OHMS 1% 1/10W	AAC CR16-1002FM
17	1	R2	RES, 0603 31.6K OHMS 1% 1/10W	AAC CR16-3162FM
18	1	R3	RES, 0603 68.1K OHMS 1% 1/10W	AAC CR16-6812FM
19	1	R4	RES, 0603 39.2K OHMS 1% 1/10W	AAC CR16-3922FM
20	0	R5	RES, 0603 0 OHMS - DO NOT STUFF	OPTION
21	1	R6	RES, 0603 0 OHM JUMPER	AAC CJ06-000JM
22	2	TP2,TP1	TURRET	TP\MMX\2308-2
23	1	U1	IC, LT1936EMS8E	LINEAR TECH. LT1936EMS8E
24	2	JP1,JP2	SHUNT	COMM CON CCIJ2MM-138G