

Item	Qty	Reference	Part Description	Manufacture / Part #
1	3	C5,C6,C7	CAP., X7R, 1000pF, 50V, 5%, 0402	AVX 04025C102JAT
2	4	C1,C2,C16,C17	CAP., X7R, 100pF, 50V, 5%, 0402	AVX 04025C101JAT
3	1	C3	CAP., X5R, 0.1uF, 10V, 10%, 0402	AVX 0402ZD104KAT
4	1	C4	CAP., TANT, 2.2uF, 10V, 20%, 3216	AVX TPSA225M010R1800
5	0	C18-C21(opt.)	CAP., 0402	
6	6	J1,J2,J3,J4,J5,J6	CONN., SMA, 50-OHM, EDGE-LANCH	E.F.JOHNSON, 142-0701-851
7	1	L1	IND., 10nH, 2%, 0402	MURATA LQP15MN10NG02D
8	0	L2 (opt.)	IND., 0402	
9	1	R1	RES., 4.3 Ohm, 5%, 1/16W, 0402	AAC CR05-4R3JM
10	1	R2	RES., 100K, 5%, 1/16W, 0402	AAC CR05-104JM
11	1	R3	RES., 1K, 5%, 1/16W, 0402	AAC CR05-102JM
12	3	TP1,TP2,TP3	TESTPOINT, TURRET, .094"	MILL-MAX, 2501-2
13	1	T1	HYBRID BALUN, 1900MHz, 1:4	MURATA LDB311G9020C-452
14	1	T2	HYBRID BALUN, 1900MHz, 1:2	MURATA LDB311G9005C-300
15	1	U1	IC, LT5515EUF	LINEAR TECH., LT5515EUF
16	1		FAB, PRINTED CIRCUIT BOARD	DEMO CIRCUIT #844D