

Item	Qty	Ref - Des	Description	Manufacturer's Part Number
1	1	C1	CAP, 0603 4.7uF 20% X5R	TDK C1608X5R0J475MT
2	1	C2	CAP, PHOTOFLASH, 13uF 330V	RUBYCON 330FW13AST6.3X25
3	1	C3	CAP, 1206 0.033uF 10% 630V X7R	TDK C3216X7R2J333K
4	2	C4,C5	CAP, 0402 0.1uF 20% 16V X5R	AVX 0402YD104MAT2A
5	1	C6	CAP, 0603 2.2uF 10% X5R	TDK C1608X5R1A225KT
6	1	CIN	CAP, 0805 10uF 20% 6.3V X5R	TAIYO YUDEN JDK212BJ106MG
7	1	D1	DIODE, DUAL	VISHAY GSD2004S
8	1	D4	LED, DUAL RED/GRN	LITEON LTST-C155KGJRKT
9	1	D5	DIODE, SCHOTTKY	DIODES INC. BAT54W
10	1	FT1	FLASHTUBE, FTA	PERKIN ELMER FTA160709
11	1	JP1	HEADER, 3PIN DOUBLE ROW	COMM CON 2202S-06G2
12	1	Q1	STROBE-FLASH, IGBT	RENESAS CY25BAH-8F
13	1	Q2	XSTR, MOSFET PN-CHANNEL,.DUAL	VISHAY SILICONIX Si1501DL
14	3	R1,R8,R9	RES, 0402 1K OHMS 5% 1/16W	AAC CR05-102JM
15	1	R2	RES, 0402 100 OHMS 5% 1/16W	AAC CR05-101JM
16	2	R10,R3	RES, 0402 510K OHMS 5% 1/16W	AAC CR05-514JM
17	1	R4	RES, 0402 30 OHMS 5% 1/16W	AAC CR05-300JM
18	1	R5	RES, 0402 20K OHMS 5% 1/16W	AAC CR05-203JM
19	1	R6	RES, 0402 10K OHMS 5% 1/16W	AAC CR05-103JM
20	1	R7	RES, 0402 100K OHMS 5% 1/16W	AAC CR05-104JM
21	1	R11	RES, 0402 1M OHMS 5% 1/16W	AAC CR05-105JM
22	3	R12,R13,R14	RES, 0402 0 OHM JUMPER	AAC CJ05-000M
23	3	S1,S2,S3	SWITCH, MOMENTARY	PANASONIC EVQPJS05K
24	6	TP1,TP2,TP3,TP4,TP5,TP6	TURRET	MILL MAX 2501-2
25	1	T1	XFMR, PHOTOFLASH CAP.	TDK LDT565630T-001
26	1	T2	XFMR, TRIGGER	TOKYO COIL ENG'R BO-02
27	1	U1	IC, LT3484EDCB-0	LINEAR TECH LT3484EDCB-0
28	1	U2	IC, PIC16F630-I/ST	MICRO CHIP PIC16F630-I/ST
29	4		LOCKING SPACERS	MICRO PLASTICS 27MSP00250
30	2		SOLDER TERMINAL, SLOTTED	MILL MAX 2104-2-01-01-00-00-07-0
31	4		STAND-OFF, NYLON	KEYSTONE 8831
32	1		COVER, PLASTIC	LINEAR TECH LS796A
33	1		SHUNT	SAMTEC 2SN-BK-G