



REVISIONS			
REV	DESCRIPTION	APPR	DATE

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISH ON OUTER LAYERS.
1 OZ. COPPER FINISH ON INNER LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
0.000 ARE PRIMARY DATUMS.
3. SIZE: DIMENSIONS AND TOLERANCES SHOWN.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
IMMERSION SILVER SOLDER PLATING
6. SILKSCREEN : BOTH SIDES USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING:




Component Side

SIZE	QTY	SYM	PLTD	TOL
0.07	2	□	NO	+/-0.003
0.095	4	◇	YES	+/-0.003
0.01	126	⊗	YES	+/-0.003
0.035	6	⊕	YES	+/-0.003
0.065	12	+	YES	+/-0.003

Fabrication Drawing

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ± 1
2 PLACE ± .01 3 PLACE ± .005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

APPROVALS		INIT		DATE	
DRAWN	CHECK				
DESIGN	ENGR	Helen	Walker	4/03/07	4/03/07
SCALE = NONE		DES-250		SHT 1 of 1	



1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408)432-1900

TITLE:
LT3496EUF, Triple Step-Down LED Driver

SIZE A DEMO DC986A REV. A