

IOSTEP
CLK PG00D
E10 E5



www.linear.com

(408) 432-1900

LTC CONFIDENTIAL -
FOR CUSTOMER USE ONLY

VOUT ()
J6 ()

VOUT
E12

VOUT
ADJ./5A MAX
E7

JP1 1.0V
JP2 1.2V
JP3 1.5V
JP4 1.8V
JP8 2.5V
JP9 3.3V
JP10 5.0V

TRACK
E8

C11

C16 U1
C2



MODE
JP6
DCM
CCM

E13
GND

E9
GND

IOSTEP ()
J5 ()
LTM4624
4A STEP-DOWN
μMODULE® REGULATOR
DEMO CIRCUIT 1889A

ON
OFF
JP7 RUN

VIN E6
VIN 4V-14V E2
VIN C14 E4
E11
GND

LINEAR TECHNOLOGY CORP. TOP SILKSCREEN

DC1889A

DATE: 2-13-13