

IOSTEP
CLK PG00D



www.linear.com

(408) 432-1900

LTC CONFIDENTIAL -
FOR CUSTOMER USE ONLY

VOUT ()
J6 ()
VOUT

TRACK

VOUT
ADJ./5A MAX

PHMODE
2 PHASE
3 PHASE
4 PHASE
JP5

JP1 1.0V
JP2 1.2V
JP3 1.5V
JP4 1.8V
JP8 2.5V
JP9 3.3V
JP10 5.0V

CLKIN

C11

U1
C16 C2

CLKOUT



MODE
JP6
DCM
CCM

GND

GND IOSTEP ()
J5 ()
LTM462
STEP-DOWN
µMODULE® REGULATOR
DEMO CIRCUIT 2171A-
ON OFF RUN
JP7

VIN C14

VIN 4V-20V GND GND

LINEAR TECHNOLOGY CORP. TOP SILKSCREEN

DC2171A

DATE: 10-30-13