



REV 1

U4
54AA05
1.0uF
C1

R3
1.30K
100uF
C4
10.0K
R7
10.0K
R2
10.0K
R6
10.0K
R5
10.0K
R1
10.0K

100uF
C12
10.0K
R2
5.2uF
C13

BT0
BT1
BT3
BT5
BT6
BT7
BT8

R4
R12
R14