

	A	B	C	D	E
1	Item	Qty	Ref - Des	Desc	Manufacturer's Part Number
2	1	1	CIN1	CAP, 150uF 25% 25V ALUM	SUN ELEC. IND. CORP. 35HVVH150M
3	2	16	CIN2,CIN3,CIN4,CIN5,CIN6,	CAP, 1210 22uF 10% 25V X5R	AVX 1210D226KAT2A
4			CIN7,CIN8,CIN9,CIN10,CIN11,		
5			CIN12,CIN13,CIN14,CIN15,		
6			CIN16,CIN17		
7	3	21	CO1,CO2,CO3,CO4,CO7,CO8,	CAP, 1210 100uF 20% 6.3V X5R	MURATA GRM32ER60J107ME20L
8			CO9,CO10,CO11,CO14,CO15,		
9			CO16,CO17,CO18,CO21,CO22,		
10			CO23,CO24,CO25,C31,C32		
11	4	8	CO5,CO6,CO12,CO13	CAP, 7343 470uF 20% 4V POSCAP	PANASONIC 4TPE470MCL
12			CO19,CO20,CO26,CO27		
13	5	4	C1,C14,C19,C24	CAP, 1206 22uF 10% 10V X7R	MURATA GRM31CR71A226KE15L
14	6	4	C2,C15,C20,C25	CAP, 0805 4.7uF 20% 25V X5R	MURATA GRM21BR61E475MA12L
15	7	0	C4,C5,C7,C16,C18,C21,C23,	CAP, 0603 OPTION	OPTION
16			C26,C28		
17	8	4	C6,C17,C22,C27	CAP, 0603 2200pF 10% 50V X7R	AVX 06035C222KAT2A
18	9	1	C8	CAP, 0603 100pF 10% 50V X7R	AVX 06035C101KAT2A
19	10	2	C9,C10	CAP, 0603 0.47uF 10% 10V X7R	MURATA GRM188R71A474KA61D
20	11	2	C29,C30	CAP, 0805 10uF 10% 6.3V X5R	MURATA GRM219R60J106KE19D
21	12	1	C33	CAP, 0603 1uF 10% 16V X7R	AVX, 0603YC105KAT2A
22	13	27	E1,E2,E3,E5,E6,E9,E10,E11,E12,	TURRET	MILL MAX 2308-2-00-80-00-00-07-0
23			E13,E14,E15,E17,E18,E19,E24,		
24			E25,E27,E30,E31,E32,E34,E37,		
25			E38,E39,E43,E44		
26	14	2	E7,E8	TURRET	MILL MAX 2501-2-00-80-00-00-07-0
27	15	6	J1,J2,J5,J6,J7,J8	LUG RING, #10	KEYSTONE 8205
28	16	12	J1,J2,J5,J6,J7,J8	NUT, BRASS 10-32	ANY #10-32
29	17	1	JP1	HEADER, 4PIN, 2mm	SAMTEC TMM-104-02-L-S
30	18	1	JP2	HEADER, 3PIN 2mm	SAMTEC TMM-103-02-L-S
31	19	6	J1,J2,J5,J6,J7,J8	WASHER, #10 TIN PLATED BRASS	ANY #10 EXT BZ TN
32	20	6	J1,J2,J5,J6,J7,J8	STUD	PEM KFH-032-10
33	21	2	J3,J4	CON, SMA	MOLEX 73391-0060
34	22	4	MH1,MH2,MH3,MH4	STANDOFF, SNAP ON	KEYSTONE_8831
35	23	1	Q3	XSTR, MOSFET N-CHANNEL	VISHAY SILICONIX SUD50N04-8M8P-4GE
36	24	0	R1,R11,R3,R13,R16,R21,R43,R44,	RES, 0603 OPTION	OPTION
37			R48,,R52,R53,R57,R61,R63,R66		
38			R71,R72,R73,R74		

	A	B	C	D	E
39	25	13	R2,R17,R19,R45,R47,R50,R54,	RES, 0603 0 OHM	VISHAY CRCW06030000Z0EA
40			R56,R59,R62,R65,R68,R69		
41	26	4	R4,R5,R12,R15	RES, 0603 10K OHMS 5% 0.1W	VISHAY CRCW060310K0JNEA
42	27	1	R7	RES, 2010 0.01OHMS 1% 1W	VISHAY WSL2010R0100FEA18
43	28	2	R8,R9	RES, 0603 51 OHMS 5% 0.1W	VISHAY CRCW060351R0JNEA
44	29	1	R14	RES, 0603 10K OHMS 1% 0.1W	VISHAY CRCW060310K0FKEA
45	30	4	R18,R49,R58,R67	RES 0805 2.2 OHMS 5% 0.125W	VISHAY CRCW08052R20JNEA
46	31	1	R20	RES, 0603 4.99K OHMS 1% 0.1W	VISHAY CRCW06034K99FKEA
47	32	4	R22,R51,R60,R70	RES, 0603 34.8K OHMS 1% 0.1W	VISHAY CRCW060334K8FKEA
48	33	4	R24,R26,R32,R37	RES, 2010 0 OHM	VISHAY CRCW20100000Z0EF
49	34	1	R76	RES, 2010 0 OHM	VISHAY WSL201000000ZEA9
50	35	1	R25	RES, 2512 0 OHM	VISHAY WSL251200000ZEA9
51	36	4	U1,U2,U3,U4	IC, HIGH EFFICIENCY 34A POWER MODULE	LINEAR TECH. LTM4636EY
52	37	2	XJP1,XJP2	SHUNT 2mm	SAMTEC 2SN-BK-G