




SDRMASKTOP\_PG SDRMASKTOP\_BG




ETCH TOP




L2\_GND PLANE LAYER 2




ETCH\_L3 LAYER 3



ETCH\_L4 LAYER4




ETCH\_L5 LAYER5




L6\_V3V POWER PLANE LAYER 6







ETCH\_L7LAYER 7




ETCH\_L8 LAYER8




L9\_GND PLANE LAYER 9




BOTTOM\_ETCH



SDRMASKBOT\_BG SDRMASKBOT\_PG





HOLE CHART				
ALL UNITS ARE IN MILS				
FIGURE	SIZE	TOLERANCE	PLATED	QTY
.	4.0	+0.0/-4.0	PLATED	140
.	10.0	+0.0/-10.0	PLATED	9
.	10.0	+3.0/-10.0	PLATED	775
•	34.0	+2.0/-2.0	PLATED	1
•	36.0	+3.0/-3.0	PLATED	164
•	41.0	+3.0/-3.0	PLATED	61
▲	41.0	+3.0/-3.0	PLATED	17
•	42.0	+3.0/-3.0	PLATED	2
■	42.0	+3.0/-3.0	PLATED	19
•	42.0	+3.0/-3.0	PLATED	10
▲	48.0	+3.0/-3.0	PLATED	13
■	50.0	+3.0/-3.0	PLATED	9
c	71.0	+3.0/-3.0	PLATED	2
F	105.0	+3.0/-3.0	PLATED	2
G	120.0	+3.0/-3.0	PLATED	5
H	120.0	+3.0/-3.0	PLATED	3
■	40.0	+3.0/-3.0	NON-PLATED	9
L	47.0	+3.0/-3.0	NON-PLATED	2
N	61.0	+2.0/-2.0	NON-PLATED	2
P	130.0	+3.0/-3.0	NON-PLATED	2
Q	140.0	+3.0/-3.0	NON-PLATED	4

