


|  |                         |
|--|-------------------------|
| MAX17544 - 3.3V OUTPUT EVKIT   |                         |
| P/N: EPCB17544A  | REV<br>A                |
|  <b>maxim<br/>integrated™</b> |                         |
| LAYER<br>LAYER 3   |                         |
| DATE:  | ALL UNITS ARE IN 0.001" |

