

D

C

B

A

D

C

B

A

| | | | | | |
|---------------------------------------|--|--|--|--|--|
| TOLERANCES UNLESS OTHERWISE SPECIFIED | | THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO MAXIM. THE INFORMATION IN THIS DOCUMENT IS NOT TO BE SHOWN, REPRODUCED, OR DISCLOSED TO ANYONE OUTSIDE OF MAXIM, WITHOUT PRIOR WRITTEN PERMISSION FROM MAXIM. | | <div><div></div><div>maxim integrated™</div></div> | |
| FRACTIONS +/- | | DECIMALS .XX +/- .01 .XXX +/- .005 | | ANGLES +/- | |
| MATERIAL: | | DRAWN BY: ST | | DATE: 10/21/2021 | |
| SEE NOTES | | CHECKED BY: | | DATE: | |
| FINISH: | | APPR. BY: | | DATE: | |
| SEE NOTES | | APPR. BY: | | DATE: | |
| | | MAX22514_EVKIT_A | | REV A | |
| | | HARDWARE NUMBER: XX-XXXX-XXX | | | |
| | | NOT TO SCALE | | TEMPLATE REV: SHEET 1 OF 1 | |