




PKG. CODES	POD
[X256-2 / X256+2]	21-0351
[X256-3 / X256+3]	21-0499
[X256-7 / X256+7] [X256T-1 / X256T+1] [X256T-2 / X256T+2] [X256T-3 / X256T+3] [X256T-4 / X256T+4] [X25677-12 / X25677+12]	21-0315
[X25677-10 / X25677+10]	21-0474
[X25677-13 / X25677+13]	21-0496
[X25677-11 / X25677+11] [X25677-14 / X25677+14]	21-0465

NOTES:

1. REFERENCE PKG. OUTLINE: PLEASE SEE TABLE ABOVE.
2. LAND PATTERN COMPLIES TO: IPC7351A.
3. TOLERANCE: ± 0.02 MM.
4. ALL DIMENSIONS APPLY TO BOTH LEADED (-) AND PbFREE (+) PKG. CODES.
5. ALL DIMENSIONS IN MM.

—DRAWING NOT TO SCALE—

This document (including dimensions, notes & specs) is a recommendation based on typical circuit board manufacturing parameters. Since land pattern design depend on many factors unknown to Maxim (eg. user's board manufacturing specs), user must determine suitability for use. This document is subject to change without notice. Contact technical support at <http://www.maxim-ic.com/support> for further questions.

MAXIM

TITLE:

PACKAGE LAND PATTERN, [X256, X256T, X25677] 17x17mm CSBGA, 256 BALLS

APPROVAL

DOCUMENT CONTROL NO.
90-0291

REV.
D

1/1