




SIDE VIEW - 1




SIDE VIEW - 3




TOP VIEW



SIDE VIEW - 4



BOTTOM VIEW



SIDE VIEW - 2

MILLIMETERS			
A	0.96	1.08	1.20
A1	0.00	-	0.05
A2	0.55	0.60	0.65
b	0.06	0.08	0.10
Rc	0.20	0.25	0.30
D	2.87	3.00	3.13
E	2.87	3.00	3.13
D2	2.67	2.70	2.73
E2	2.67	2.70	2.73
F	2.75	2.80	2.85
d	0.47	0.60	0.73
e	0.62	0.75	0.88
h	0.47	0.60	0.73
m	1.07	1.20	1.33
n	0.62	0.75	0.88

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. GOLD PLATE 0.75um MIN. OVER 2.0um MIN NICKEL.
3. LID MATERIAL: Fe-Ni-Co, ALLOY (KV-2).
4. LID PLATING: 2.0-5.0um ELECTROLYTIC NICKEL.
5. NTK SPECIFICATION YS-1021 SHALL APPLY.
6. ALL TOLERANCES ARE ±0.13 UNLESS OTHERWISE SPECIFIED.
7. PACKAGE CODE: L8-1

-DRAWING NOT TO SCALE-



TITLE:
PACKAGE OUTLINE, 8L, CERAMIC SUBSTRATE,
3X3X1.1MM SIDEBRAZE

APPROVAL

DOCUMENT CONTROL NO.
21-100203

REV. A 1/1