




COMMON DIMENSIONS			
	MIN.	NOM.	MAX.
A	1.700	-	1.900
A1	0.140	-	0.240
A2	1.65 REF		
A3	1.350 REF		
b	0.200	-	0.300
D	7.200 ± 0.100		
E	9.900 ± 0.100		
D1	6.500 BASIC		
E1	9.000 BASIC		
e	0.500 BASIC		
SD	0.250 BASIC		
SE	0.000 BASIC		
DEPOPULATED BUMPS: NONE			



- NOTES:
1. Terminal pitch is defined by terminal center to center value.
 2. Outer dimension is defined by center lines between scribe lines.
 3. All dimensions in millimeter.
 4. Marking shown is for package orientation reference only.

- DRAWING NOT TO SCALE -


**maxim
integrated™**

TITLE: PACKAGE OUTLINE 266 BUMPS eWLB PKG. 0.5 mm PITCH, M2667A9M#1 & M2667A9M#2		
APPROVAL	DOCUMENT CONTROL NO. 21-100320	REV. B 1/1