



TOP VIEW



SIDE VIEW



BOTTOM VIEW

	SYMBOL	MIN	NOM	MAX
TOTAL THICKNESS	A	0.5	0.55	0.6
STAND OFF	A1	0	0.02	0.05
MOLD THICKNESS	A2	---	0.4	---
L/F THICKNESS	A3	0.152 REF		
LEAD WIDTH	b	0.15	0.2	0.25
BODY SIZE	X	D	3 BSC	
	Y	E	2.5 BSC	
LEAD PITCH	e	0.4 BSC		
LEAD LENGTH	L1	0.35	0.4	0.45
	L2	1.60	1.65	1.70
PACKAGE EDGE TOLERANCE	aaa	0.1		
MOLD FLATNESS	ccc	0.1		
COPLANARITY	eee	0.05		
LEAD OFFSET	bbb	0.1		

NOTES:

1. REFER TO JEDEC MO-220
2. COPLANARITY APPLIES TO LEADS, CORNER LEADS AND DIE ATTACH PAD
3. FINISH: Cu/EP • Sn8~20s
4. MAXIM PKG CODE : F182A3F-2
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE

-DRAWING NOT TO SCALE-



TITLE:
PACKAGE OUTLINE, 18L FC2QFN
3x2.5x0.55mm

APPROVAL	DOCUMENT CONTROL NO. 21-10230	REV. A	1/1
----------	----------------------------------	-----------	-----