



TOP VIEW




SIDE VIEW



BOTTOM VIEW

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5-2009.
3. COPLANARITY APPLIES TO THE TERMINALS AND ALL OTHER BOTTOM SURFACE METALLIZATION.
4. MARKING SHOWN IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.
7. Package code is F173A4FY+2.



* CONTROLLING DIMENSION : MM

SYMBOL	MILLIMETER		
	MIN.	NOM.	MAX.
A	0.700	0.750	0.800
A1	0.000	—	0.050
A2	0.480	0.530	0.580
A3	—	0.203	REF.
b	0.150	0.200	0.250
b1	0.180	0.250	0.300
b2	0.250	0.300	0.350
b3	0.350	0.400	0.450
D	—	3.500	BSC
D2	0.500	0.600	0.700
E	—	4	BSC
E2	0.500	0.600	0.700
L	0.450	0.550	0.650
L1	0.475	0.575	0.675
L2	0.500	0.600	0.700
L3	0.550	0.650	0.750
L4	0.650	0.750	0.850
L5	1.150	1.250	1.350
L6	1.175	1.275	1.375
L7	1.525	1.625	1.725
e	—	0.500	BSC
e1	—	0.525	BSC
e2	—	0.600	BSC
e3	—	0.650	BSC
e4	—	0.700	BSC
e5	—	1.325	BSC
K1	—	0.175	BSC
K2	—	0.250	BSC
K3	—	0.375	BSC
K4	—	0.425	BSC
K5	—	0.475	BSC
K6	—	0.550	BSC
TOLERANCES OF FORM AND POSITION			
aaa	—	0.150	
bbb	—	0.100	
ccc	—	0.100	
ddd	—	0.050	
eee	—	0.080	
fff	—	0.100	



TITLE:
PACKAGE OUTLINE, 17L, FC2QFN PKG.,
3.5X4.0X0.75mm

APPROVAL
YUANYUAN WEN

DOCUMENT CONTROL NO.
21-100538

REV. A 1/1