



TOP VIEW



SIDE VIEW



BOTTOM VIEW

DIM	MIN	NOM	MAX
A	0.900	0.950	1.000
A1	0	0.020	0.050
A2	0.203 REF.		
b	0.200	0.250	0.300
D	3.450	3.500	3.550
E	8.050	8.100	8.150
e	1.100	1.150	1.200
e1	0.450	0.500	0.550
L	1.300	1.350	1.400
L1	0.450	0.500	0.550
L2	0.550	0.600	0.650
L3	0.875 REF		
D1	2.975	3.000	3.025
E1	7.555	7.580	7.605
X	0.200	0.250	0.300
Y	0.200	0.250	0.300
Pkgcodes: P203A8F-2			

NOTES:

1. DIMENSIONING AND TOLERANCING CONFORME TO ASME Y14.5-2009.
2. ALL DIMENSIONS ARE IN MILLIMETERS, ANGLE IS IN DEGREES.
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. DIMENSION b APPLIES TO METALLIZED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.30mm FROM TERMINAL TIP. IF THE TERMINAL HAS THE OPTIONAL RADIUS ON THE OTHER END OF THE TERMINAL, THE DIMENSION b SHOULD NOT BE MEASURED IN THAT RADIUS AREA.
5. PIN #1 ID ON TOP WILL BE LASER MARKED.
6. MARKING SHOWN IF FOR PACKAGE ORIENTATION ONLY.
7. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC#10-0131.
8. ALL DIMENSIONS APPLY TO PBFREE (+) PKGCODES ONLY.

-DRAWING NOT TO SCALE-


**maxim  
integrated**

TITLE:  
PACKAGE OUTLINE, 20L FCQFN PKG.,  
8.10X3.50X0.95mm , FLIP CHIP

APPROVAL	DOCUMENT CONTROL NO. 21-100098	REV. C
		1/1