



COMMON DIMENSIONS			
DIM	MIN.	NDM.	MAX.
A	0.90	0.95	1.00
A1	0.00	---	0.05
A3	0.20 REF		
b	0.20	0.25	0.30
D	4.05	4.15	4.25
E	5.90	6.00	6.10
e	0.05 BSC		
e1	1.00 BSC		
e2	0.81 BSC		
L	1.00	1.10	1.20
L1	2.025	2.125	2.225
L2	1.825	1.925	2.025
L3	0.90	1.00	1.10
L4	1.10	1.20	1.30
N	17		
aaa	0.08		
bbb	0.1		

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5M -2009
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. PIN #1 ID ON TOP WILL BE LASER MARKED.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PARTS.
7. PACKAGE CODES: P174A6F+1



TITLE:
PACKAGE OUTLINE 17L FC-QFN PKG
4.15x6.00x0.95mm

APPROVAL	DOCUMENT CONTROL NO. 21-100191	REV. A	1/1
----------	-----------------------------------	-----------	-----

-DRAWING NOT TO SCALE-