





TOP VIEW



SIDE VIEW



BOTTOM VIEW



| COMMON DIMENSIONS | | | |
|-------------------|----------|-------|-------|
| DIM | MIN. | NDM. | MAX. |
| A | 0.90 | 0.95 | 1.00 |
| A1 | 0.00 | --- | 0.05 |
| A3 | 0.20 REF | | |
| b | 0.20 | 0.25 | 0.30 |
| D | 4.05 | 4.15 | 4.25 |
| E | 8.90 | 9.00 | 9.10 |
| e | 0.05 BSC | | |
| e1 | 1.00 BSC | | |
| e2 | 0.81 BSC | | |
| L | 1.00 | 1.10 | 1.20 |
| L1 | 2.025 | 2.125 | 2.225 |
| L2 | 1.825 | 1.925 | 2.025 |
| L3 | 0.90 | 1.00 | 1.10 |
| L4 | 1.10 | 1.20 | 1.30 |
| N | 23 | | |
| aaa | 0.08 | | |
| bbb | 0.1 | | |

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5M -2009
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. PIN #1 ID ON TOP WILL BE LASER MARKED.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbfREE (+) PARTS.
7. PACKAGE CODES: P234A9F+1

-DRAWING NOT TO SCALE-



TITLE:
PACKAGE OUTLINE 23L FC-QFN PKG
4.15x9.00x0.95mm

| | | |
|----------------------------------|-----------|-----|
| PACKAGE OUTLINE NO. 21-100192 | REV. A | 1/1 |
|----------------------------------|-----------|-----|