



TOP VIEW



SIDE VIEW




BOTTOM VIEW

DIMENSION TABLE			
SYMBOL	MIN	NOM	MAX
A	---	2.80	2.90
A1	0.26	0.30	0.34
A2	2.50 REF		
D	9.35 BSC		
E	11.50 BSC		
W	0.60	0.65	0.70
L	0.60	0.65	0.70
e	1.15 BSC		
N	32		
D1	5.75 BSC		
E1	8.05 BSC		
aaa	0.100		
bbb	0.100		
ccc	0.100		

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5M -2009
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. PIN #1 ID ON TOP WILL BE LASER MARKED.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PARTS.
7. PACKAGE CODE: L3211A9M+1

-DRAWING NOT TO SCALE-

		
TITLE: PACKAGE OUTLINE, 32L, LGA HYBRID 11.5x9.35x2.8 mm		
APPROVAL DAVID PRUITT	DOCUMENT CONTROL NO. 21-100541	REV. A 1/1