


	SYMBOL	COMMON DIMENSIONS		
		MIN.	NDR.	MAX.
TOTAL THICKNESS	A	1.69	1.75	1.8
SUBSTRATE THICKNESS	A1	---	---	0.25
MOLD THICKNESS	A2	1.5		REF
BODY SIZE	D	5.5		BSC
	E	6.5		BSC
LEAD WIDTH	W1	0.45	0.5	0.55
	W2	0.43	0.48	0.53
LEAD LENGTH	L1	0.54	0.59	0.64
	L2	0.43	0.48	0.53
LEAD PITCH	e	1		BSC
LEAD COUNT	n1	18		
	n2	4		
EDGE LEAD CENTER TO CENTER	D1	4.98		BSC
	E1	5.98		BSC
BODY CENTER TO CONTACT LEAD	SD	0.5		BSC
	SE	---		BSC
PACKAGE EDGE TOLERANCE	aaa	0.1		
MOLD FLATNESS	lbbb	0.2		
COPLANARITY	dddd	0.08		



- NOTES:
1. PARALLELISM MEASUREMENT SHALL EXCLUDE ANY EFFECT OF MARK ON TOP SURFACE OF PACKAGE.
 2. DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
 3. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC # 10-0131.
 4. MARKING SHOWN IS FOR PKG. ORIENTATION ONLY.
 5. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE.
 6. PACKAGE CODE: L226A5-1



TITLE:
PACKAGE OUTLINE, 22L LGA,
6.5x5.5x1.8 mm, 1mm PITCH

APPROVAL

DOCUMENT CONTROL NO.
21-100462

REV. 1
A 1/1

-DRAWING NOT TO SCALE-