



SYMBOL	COMMON DIMENSIONS		
	MIN.	NOR.	MAX.
A	1.4	1.5	1.6
A1		0.3	REF
A2		0.985	REF
A3		0.2	REF
D	6.9	7	7.1
E	3.4	3.5	3.6
W	0.45	0.5	0.55
L	0.65	0.7	0.75
e		1	BSC
n		14	
D1		6	BSC
E1		2.6	BSC
aaa		---	
bbb		---	
ddd		0.08	

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5M -2009
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. PIN #1 ID ON TOP WILL BE LASER MARKED.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PARTS.
7. PACKAGE CODES: F143H7MK-1



TITLE:  
PACKAGE OUTLINE, 14L OLGA,  
3.5x7x1.5mm

APPROVAL

DOCUMENT CONTROL NO.  
21-100325

REV.  
B

1/1

-DRAWING NOT TO SCALE-