


TOP VIEW

SIDE VIEW



BOTTOM VIEW

| SYMBOL | COMMON DIMENSIONS | | |
|--------|-------------------|------|------|
| | MIN. | NOR. | MAX. |
| A | 0.99 | 1.09 | 1.19 |
| A1 | | 0.19 | REF |
| A2 | | 0.75 | REF |
| A3 | | 0.1 | REF |
| D | 5.5 | 5.6 | 5.7 |
| E | 3.2 | 3.3 | 3.4 |
| W | 0.25 | 0.3 | 0.35 |
| L | 0.75 | 0.8 | 0.85 |
| e | | 0.5 | BSC |
| n | | 22 | |
| D1 | | 5 | BSC |
| E1 | | 2.2 | BSC |
| aaa | | 0.1 | |
| bbb | | 0.2 | |
| ddd | | 0.08 | |

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5M -2009
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. PIN #1 ID ON TOP WILL BE LASER MARKED.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PARTS.
7. PACKAGE CODES: F223D5+1

-DRAWING NOT TO SCALE-



TITLE:
PACKAGE OUTLINE, 22L OLGA,
3.3x5.6x1.09mm

APPROVAL
YUANYUAN WEN

DOCUMENT CONTROL NO.
21-100142

REV. A 1/1