



TOP VIEW



SIDE VIEW



BOTTOM VIEW

SYMBOL	COMMON DIMENSIONS		
	MIN.	NOR.	MAX.
A	0.745	0.845	0.945
A1		0.26	REF
A2		0.37	REF
A3		0.2	REF
D	3.9	4	4.1
E	4.4	4.5	4.6
W	0.35	0.4	0.45
L	0.35	0.4	0.45
e		0.65	BSC
n		20	
D1		2.6	BSC
E1		2.6	BSC
aaa		0.1	
bbb		---	
ddd		0.08	

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5 -2009
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. PIN #1 ID ON TOP WILL BE LASER MARKED.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PARTS.
7. PACKAGE CODES: F204A4-1

-DRAWING NOT TO SCALE-



TITLE:
PACKAGE OUTLINE, 20L OLGA,
4x4.5x0.845mm

APPROVAL
YUANYUAN WEN

DOCUMENT CONTROL NO.
21-100231

REV. B 1/1