



TOP VIEW



SIDE VIEW



BOTTOM VIEW

SYMBOL	COMMON DIMENSIONS		
	MIN.	NOM.	MAX.
A	1	1.1	1.2
A1		0.2	REF
A2		0.65	REF
A3		0.2	REF
D	5.5	5.6	5.7
E	3.2	3.3	3.4
W	0.25	0.3	0.35
L	0.65	0.7	0.75
e		0.8	BSC
n		14	
D1		4.8	BSC
E1		2.4	BSC
aaa		0.1	
bbb		0.2	
ddd		0.08	

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5M -2009
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. PIN #1 ID ON TOP WILL BE LASER MARKED.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PARTS.
7. PACKAGE CODES: F143E5-1



TITLE:  
PACKAGE OUTLINE, 14L OLGA,  
3.3x5.6x1.1mm

APPROVAL  
YUANYUAN WEN

DOCUMENT CONTROL NO.  
21-100239

REV. 1  
A

-DRAWING NOT TO SCALE-