



TOP VIEW



SIDE VIEW



BOTTOM VIEW

SYMBOL	COMMON DIMENSIONS		
	MIN.	NOR.	MAX.
A	1.3	1.4	1.5
A1		0.3	REF
A2		0.885	REF
A3		0.2	REF
D	4.2	4.3	4.4
E	2.8	2.9	3
W	0.35	0.4	0.45
L	0.55	0.6	0.65
e		0.6	BSC
n		14	
D1		3.6	BSC
E1		1.9	BSC
aaa		---	
bbb		---	
ddd		0.08	

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5M-2009
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. PIN #1 ID ON TOP WILL BE LASER MARKED.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbfREE (+) PARTS.
7. PACKAGE CODES: F142A4+1



TITLE:
PACKAGE OUTLINE, 14L OLGA,
2.9x4.3x1.4mm

APPROVAL
YUANYUAN WEN

DOCUMENT CONTROL NO.
21-100309

REV. 1
B 1/1