



1
TOP VIEW



SIDE VIEW



END VIEW

DIM.	INCHES		MM	
	MIN.	MAX.	MIN.	MAX.
A	.072	.084	1.83	2.13
A1	.002	.010	0.051	0.250
A2	.068	.070	1.73	1.78
b	.013	.020	0.33	0.51
c	.006	.010	0.15	0.25
D	.203	.215	5.16	5.46
E1	.203	.213	5.16	5.41
e	.050 BSC		1.27 BSC	
H	.302	.318	7.67	8.07
L	.019	.030	0.48	0.76
α	0°	8°	0°	8°
PKG. CODE	W8+2, W8MK+2, W8+4, W8MS+1			

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC # 10-0131.
3. THE CHAMFER ON THE BODY IS OPTIONAL.
4. IF IT IS NOT PRESENT, A TERMINAL 1 IDENTIFIER MUST BE POSITIONED SO THAT 1/2 OR MORE OF IT'S AREA IS CONTAINED IN THE HATCHED ZONE.
5. ALL DIMENSIONS APPLY TO BOTH LEADED (-) AND PbFREE (+) PKG. CODES.

-DRAWING NOT TO SCALE-



TITLE:
PACKAGE OUTLINE,
8L SOIC, .208 INCH

APPROVAL
Chintankumar Patel

DOCUMENT CONTROL NO.
21-0262

REV. E 1/1