



COMMON DIMENSIONS	
A	0.50 MAX
A1	0.19 ±0.03
A2	0.28 REF
A3	0.04 BASIC
b	∅0.27 ±0.03
D	2.728 ±0.025
E	2.708 ±0.025
D1	2.00 BASIC
E1	2.00 BASIC
e	0.40 BASIC
SD1	0.234 BASIC
SD2	0.166 BASIC
SE1	0.228 BASIC
SE2	0.172 BASIC
DEPOPULATED BUMPS: NONE	



- NOTES:
1. Terminal pitch is defined by terminal center to center value.
 2. Outer dimension is defined by center lines between scribe lines.
 3. All dimensions in millimeter.
 4. Marking shown is for package orientation reference only.
 5. Tolerance is ± 0.02 unless specified otherwise.
 6. All dimensions apply to PbFree (+) package codes only.
 7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -


**maxim
integrated™**

TITLE PACKAGE OUTLINE 36 BUMPS
THIN WLP PKG. 0.4 mm PITCH,N362D2+1

APPROVAL	DOCUMENT CONTROL NO. 21-100413	REV. C	1/1
----------	-----------------------------------	-----------	-----