



SYMBOL	MIN	MAX
A	--	1.10
A1	0.05	0.15
A2	0.85	0.95
b	0.19	0.30
c	0.09	0.18
D	2.90	3.10
E	4.40 NOM.	
e	0.65 BSC.	
G	0.25 REF.	
H	6.25	6.55
L	0.50	0.70
α	0°	8°
PKG CODE	H8-1, H8-2, H8-3	



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC # 10-0131.
3. DIMENSION "D" DOES NOT INCLUDE MOLD MISMATCH, FLASH OR PROTRUSIONS.
4. LEAD CENTERSLINES TO BE AT TRUE POSITION AS DEFINED BY BASIC DIMENSION "e", +/- 0.05.
5. MARKING IS FOR PACKAGE ORIENTATION REFERENCE.
6. LEADS TO BE COPLANAR WITHIN 0.10 MM.
7. MEETS JEDEC MO-153.
8. ALL DIMENSIONS APPLY TO BOTH LEADED (-) AND PbFREE (+) PKG. CODES.

-DRAWING NOT TO SCALE-

MAXIM			
TITLE: PACKAGE OUTLINE, 8L TSSOP, 4.40mm BODY			
APPROVAL RAMON DE LEON 02/17/10	DOCUMENT CONTROL NO. 21-0175	REV. B	1/1