



TOP VIEW



SIDE VIEW

COMMON DIMENSIONS	
A	0.64±0.05
A1	0.24±0.03
A2	0.40 REF
A3	0.025 BASIC
b	ø0.31±0.03
D1	2.50 BASIC
E1	2.50 BASIC
e	0.50 BASIC
SD	0.25 BASIC
SE	0.25 BASIC




BOTTOM VIEW

PKG. CODE	E		D		DEPOPULATED BUMPS
	MIN	MAX	MIN	MAX	
W363A3+1	2.95	3.18	2.95	3.18	NONE
W363A3+2	2.95	3.18	2.95	3.18	B3,B4,E3,E4
W363A3+3	2.95	3.18	2.95	3.18	C3,C4,D3,D4

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeters.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02mm unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front-side finish can be either Black or Clear.

-DRAWING NOT TO SCALE-



TITLE:  
PACKAGE OUTLINE  
36 BUMPS, WLP PKG. 0.5mm PITCH

APPROVAL TIE WANG 10/09/09	DOCUMENT CONTROL NO. 21-0024	REV. D	1/1
----------------------------------	---------------------------------	-----------	-----