




COMMON DIMENSIONS	
A	0.64 ±0.05
A1	0.19 ±0.03
A2	0.45 REF
b	∅0.27 ±0.03
D1	0.80 BASIC
E1	0.40 BASIC
e	0.40 BASIC
SD	0.00 BASIC
SE	0.20 BASIC
DEPOPULATED BUMPS: NONE	



PKG. CODE	Part No.	A3	D	E
W61B1+1	Overall Spec	N/A	1.270±0.100	0.865±0.105
	MAX44264 / MAX44265 / MAX4470 / MAX9911	0.040 BASIC	1.314±0.025	0.907 ±0.025
	MAX2203	0.025 BASIC	1.238±0.025	0.831 ±0.025
	MAX2657 / MAX2658 / MAX2667 / MAX2669 / MAX2674 / MAX2676		1.228±0.025	0.827 ±0.025
W61F0+1			1.235±0.015	0.835±0.015

- NOTES:
1. Terminal pitch is defined by terminal center to center value.
 2. Outer dimension is defined by center lines between scribe lines.
 3. All dimensions in millimeter.
 4. Marking shown is for package orientation reference only.
 5. Tolerance is ± 0.02 unless specified otherwise.
 6. All dimensions apply to PbFree (+) package codes only.
 7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -


**maxim
integrated™**

TITLE PACKAGE OUTLINE 6 BUMPS
WLP PKG. 0.4 mm PITCH

APPROVAL	DOCUMENT CONTROL NO. 21-0217	REV. G	1/1
----------	---------------------------------	-----------	-----