



TOP VIEW



SIDE VIEW

COMMON DIMENSIONS	
A	0.64 ±0.05
A1	0.19 ±0.03
A2	0.45 REF
A3	0.025 BASIC
b	∅0.27 ±0.03
D1	1.20 BASIC
E1	2.00 BASIC
e	0.40 BASIC
SD	0.20 BASIC
SE	0.20 BASIC

PKG. CODE	E	D	DEPOPULATED BUMPS
W241B2+1	2.57 ±0.10	1.75 ±0.10	NONE
W241C2+1	2.707 ±0.025	1.858 ±0.025	NONE
W241D2+1	2.508 ±0.025	1.897 ±0.025	NONE



BOTTOM VIEW

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -

			
<b>TITLE</b> PACKAGE OUTLINE 24 BUMPS WLP PKG. 0.40 mm PITCH			
APPROVAL TIE WANG 01/18/13	DOCUMENT CONTROL NO. 21-0219	REV. D	1/1