



TOP VIEW



SIDE VIEW

COMMON DIMENSIONS	
A	0.64±0.05
A1	0.24±0.03
A2	0.40 REF
A3	0.040 BASIC
b	∅0.31±0.03
D1	2.50 BASIC
E1	3.00 BASIC
e	0.50 BASIC
SD	0.25 BASIC
SE	0.00 BASIC

PKG. CODE	E	D	DEPOPULATED BUMPS
W423C3+1	3.53±0.08	3.075±0.075	NONE
W423D3+1	3.75±0.06	3.19±0.06	NONE
W423E3+1	3.515±0.015	3.395±0.015	NONE



BOTTOM VIEW

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeters.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02mm unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front-side finish can be either Black or Clear.

-DRAWING NOT TO SCALE-

			
TITLE:			
PACKAGE OUTLINE			
42 BUMPS, WLP PKG. 0.5 mm PITCH			
APPROVAL	DOCUMENT CONTROL NO.	REV.	1/1
	21-0440	1	