



TOP VIEW



SIDE VIEW

COMMON DIMENSIONS	
A	0.64 ±0.05
A1	0.24 ±0.03
A2	0.40 REF
A3	0.025 BASIC
b	∅0.31 ±0.03
D1	0.50
E1	0.50
e	0.50 BASIC
SD	0.25 BASIC
SE	0.25 BASIC



BOTTOM VIEW

PKG. CODE	E		D		DEPOPULATED BUMPS
	MIN	MAX	MIN	MAX	
W41A1+2	1.00	1.10	1.00	1.10	NONE
W41C1+1	1.13	1.17	1.13	1.17	NONE
W41D1+1	1.27	1.30	1.25	1.28	NONE

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.



TITLE		PACKAGE OUTLINE 4 BUMPS, WLP PKG. 0.5mm PITCH	
APPROVAL TIE WANG 07/29/11	DOCUMENT CONTROL NO. 21-0455	REV. C	1/1